UV-Visible Spectrophotometer



Brand : JASCO Model : V-530

Location : K647 Room, 6th Floor, Chaloemprakiet Building, Phyathai Campus

Custodian : PRADUP MESAWAT

Description and Specification:

Description and Specification.	
Optical system:	Double beam, single monochromator with a 1200 grooves/mm
	concave grating and modified Rowland mount
Spectral bandwidth:	2 nm
Wavelength range:	190 - 1100 nm
Light sources:	Deuterium lamp for UV range (190 - 350 nm),
	Halogen lamp for VIS range (330 - 1100 nm)
Light source switching:	Selectable within a range of 330 to 350 nm
Wavelength repeatability:	± 0.1 nm
wavelength accuracy:	± 0.5 nm
Photometric modes:	Abs, %T, %R
Photometric range:	-2 - 3 Abs Photometric
reproducibility:	± 0.001 Abs (0 - 0.5 Abs)
	± 0.002 Abs (0.5 - 1 Abs)
	± 0.15 %T
Photometric accuracy:	± 0.002 Abs (0 - 0.5 Abs)
	± 0.004 Abs (0.5 - 1 Abs)
	± 0.3 %T
	(Above figures obtained using NIST SRM 930D)
Stray light:	0.04 %T both at 220 nm with NaI 10 g/l solution and at
	340 nm with NaNO ₂ 50 g/l solution
Wavelength scan speed:	4000, 2000, 1000, 400, 200, 100, 40 nm/min

Description and Specification:

Wavelength slew speed:	8000 nm/min
Sampling interval:	0.1, 0.2, 0.5, 1, 2 nm/data (spectral scan mode)
	0.05, 0.1, 0.2, 0.5, 1, 2, 5, 10 sec/data (time scan mode)
Baseline stability:	± 0.001 Abs/hour
	Response: Slow (250 nm, lamp on longer than 60 min,
	temperature variation ± 5°C)
Baseline flatness:	± 0.001 Abs
	within 200 - 1000 nm range after baseline correction
	Response: Medium
	Scan speed: 100 nm/min
Response:	Quick, Fast, Medium, Slow
Detector:	Silicon photo-diode (S1337)

Application:

Sample Type	Solution
Mode	Fixed Wavelength Measurement
	Spectrum Measurement
	Quantitative Analysis
	Time Corse Measurement (Kinetic Measurement)